




# InnoFine

## Biopsy Needle Guides for SAMSUNG

- Integral design without any accessories
- High grade medical stainless steel
- Artificial polishing
- Supporting accurate and angle adjustable biopsy
- Matching a wide range of needle gauges
- Simple pressing, quick release



### About Us


As a China national high-tech enterprise, InnoFine are dedicated to R&D, manufacturing and sales ultrasound interventional products and consumables medical products since its establishment in 2013, providing safe and reliable, cost-effective products and overall solutions for thousands of hospitals in more than 100 countries around the world, products covering Ultrasound Needle Guides, Probe Cover, Gel, Biopsy Needle etc.

InnoFine will continue to adhere to the spirit of "Be innovative and forge ahead, Strive for excellence and perfection, Customer oriented ", and make unremitting efforts to promote the development of global interventional ultrasound field.

### Cooperation Ultrasound Brand (Part)




### Reference Sites (Part)



Classial Product (Part)



Biopsy needle guides for Samsung CA1-7A probe (Convex type probe)



Biopsy needle guides for Samsung P1-4 probe (Phased array type probe)



Biopsy needle guides for Samsung EVN4-9 probe (Endocavity type probe)



Biopsy needle guides for Samsung EC4-9 probe (Endocavity type probe)



Biopsy needle guides for Samsung CF4-9 probe (Microconvex type probe)



Biopsy needle guides for Samsung L3-12A probe (Linear type probe)

Accurate, Safe and Efficient Operation



· Attach



· Angle Adjustment



· Needle Insertion



· Detach

List of Biopsy Needle Guides for Samsung

| MODEL   | Transducer                                     | Transducer Type | Gauge Size/Guide Channel Length | MODEL                                      | Transducer                                                       | Transducer Type | Gauge Size/Guide Channel Length |
|---------|------------------------------------------------|-----------------|---------------------------------|--------------------------------------------|------------------------------------------------------------------|-----------------|---------------------------------|
| JSM-003 | CS1-4                                          | Convex          | 11-23G/3.5cm                    | JSM-120                                    | P3-8CA, PA3-8B                                                   | Phased Array    | 11-23G/3.5cm                    |
| JSM-062 | C2-6, C2-6IC                                   | Convex          | 11-23G/3.5cm                    | JSM-092                                    | PA1-5A                                                           | Phased Array    | 14-22G/3.5cm                    |
| JSM-019 | C1-4EC                                         | Convex          | 11-23G/3.5cm                    | JEM-037                                    | VR5-9                                                            | Endocavity      | 16-18G/16.5cm                   |
| JSM-083 | C2-8, CN2-8, C2-8-N, C2-8N                     | Convex          | 11-23G/3.5cm                    | JEM-063                                    | V5-9, EV3-10B                                                    | Endocavity      | 16-18G/19cm                     |
| JSM-289 | C3-7ED, C3-7IM, C3-7EP                         | Convex          | 11-23G/3.5cm                    | JEM-027                                    | ER4-9/10ED, EV4-9/10ED, EVN4-9(-H), EV4-9, ER4-9, EC4-9, EC4-9ED | Endocavity      | 16-18G/15cm                     |
| JSM-071 | CA1-7A, CA1-7AD                                | Convex          | 11-23G/3.5cm                    | JEM-011                                    | EC4-9IS, EC4-9ES, ER4-9ES                                        | Endocavity      | 16-18G/12.5cm                   |
| JSM-217 | SC1-6                                          | Convex          | 11-23G/3.5cm                    | JEM-060                                    | EA2-11B                                                          | Endocavity      | 16-18G/14.5cm                   |
| JSM-091 | C2-8A, CA2-8A, CA2-8AD, CA2-9A, CA2-9AD, CF2-8 | Convex          | 11-23G/3.5cm                    | JEM-070                                    | EA2-11AR, EA2-11AV, EA2-11ARD, EA2-11AVD, EA2-11ARE, EA2-11AVE   | Endocavity      | 16-18G/17.5cm or 11.5cm         |
| JSM-137 | CA3-10A                                        | Convex          | 11-23G/3.5cm                    | JEM-073                                    | EV2-10A                                                          | Endocavity      | 16-18G/17cm or 13cm             |
| JSM-315 | C2-5                                           | Convex          | 11-23G/3.5cm                    | JEM-081                                    | miniER7                                                          | Endocavity      | 16-18G/12.5cm                   |
| JSM-389 | CA1-7S, CA1-7SD                                | Convex          | 11-23G/3.5cm                    | JEM-022                                    | EC4-9/10ED, EC4-9/13CD, EC4-9/10R, EC4-9ED                       | Endocavity      | 16-18G/14cm                     |
| JSM-004 | L3-8, LN5-12/40                                | Linear          | 14-22G/3.5cm                    | JEM-030                                    | NEV4-9ES, NER4-9ES, E3-12A                                       | Endocavity      | 16-18G/15.5cm                   |
| JSM-103 | L5-13, L5-13IS, L7-16IS, L7-16                 | Linear          | 11-23G/3.5cm                    | JEM-054                                    | 3D4-9, 3D4-9ES                                                   | Endocavity      | 16-18G/18cm                     |
| JSM-036 | LM4-15B, LM4-15BD                              | Linear          | 11-23G/3.5cm                    | JSM-144                                    | V4-8, VE4-8                                                      | 4D              | 16G/18G/3.2cm                   |
| JSM-110 | HL5-12ED                                       | Linear          | 11-23G/3.5cm                    | JSM-161                                    | CV1-8A, CV1-8AD                                                  | 4D              | 14-22G/3.5cm                    |
| JSM-048 | L4-7, LA2-9A                                   | Linear          | 11-23G/3.5cm                    | (Please contact InnoFine for more models.) |                                                                  |                 |                                 |
| JSM-149 | LN5-12, LE5-12                                 | Linear          | 11-23G/3.5cm                    |                                            |                                                                  |                 |                                 |
| JSM-072 | L3-12A, LA3-12A, LA3-14AD, L5-13/50, LA2-14A   | Linear          | 11-23G/3.5cm                    |                                            |                                                                  |                 |                                 |
| JSM-245 | LA4-18B, LA4-18BD                              | Linear          | 11-23G/3.5cm                    |                                            |                                                                  |                 |                                 |
| JSM-090 | LA3-16A, LA3-16AD, LF5-13                      | Linear          | 11-23G/3.5cm                    |                                            |                                                                  |                 |                                 |
| JSM-322 | LA4-18A, LA4-18AD                              | Linear          | 11-23G/3.5cm                    |                                            |                                                                  |                 |                                 |
| JSM-029 | CF4-9                                          | Microconvex     | 11-23G/3.5cm                    |                                            |                                                                  |                 |                                 |
| JSM-026 | P1-4, PE2-4                                    | Phased Array    | 11-23G/3.5cm                    |                                            |                                                                  |                 |                                 |